

FISHER & PAYKEL

DATA SHEET

18" Freezer + 24" Fridge - Stainless Steel Integrated Columns

Model no:
RS1884FLJ1 / RS1884FLJK1 + RS2484SR1 / RS2484SRK1 shown.
(Various models available to swap units to opposite sides, hinge doors both left, both right or at the outsides as shown here).
(refer page 2 for metric measurements)

IMPORTANT!
For ease of installation, ensure cavity has consistent dimensions top to bottom and left to right.

Clearance Dimensions		in
Ⓐ	Overall height of cavity	84"
Ⓑ	Overall width of cavity	42"
Ⓒ	Minimum depth of cavity*	25"
Ⓓ	Width of supply area behind freezer	18"
Ⓔ	Width of supply area behind fridge	24"
Ⓕ	Height of supply area	9"
Ⓖ	Height at sides of supply area	5"
Ⓗ	Width from side of supply area	1/2"
Ⓘ	Combined width in from side of supply areas	1"
⓵	Depth of supply area	1"
Minimum door cabinetry gap clearance		1/8"


Optional Stainless Steel Panel Dimensions		in
Ⓚ	Height of door panel	79 7/8"
Ⓛ	Width of freezer door panel	17 3/4"
Ⓜ	Width of fridge door panel	23 3/4"
Ⓝ	Depth of door panels	3/4"
Ⓞ	Height of toekick panel	3 15/16"
Ⓟ	Width of toekick panel	41 7/8"

* With cavity at minimum depth, electrical and water connections must be within the supply area shown if located behind the appliance, and must not protrude from the back wall.
Connections may be located in an adjacent cabinet to either side of the fridge.

HANDLES: Handle Kits are sold separately. Shown with handle kit ADH3-RD84. Other style options available.

DATE: 10.10.2018

IMPORTANT NOTE: Throughout this guide, dimensions may vary by ±2mm (1/16"). Please read the installation manual for detailed information on installing the product. For full installation instructions & specifications visit fisherpaykel.com



ISO VIEW OF 42" CAVITY
(18" + 24")

FISHER & PAYKEL

DATA SHEET

18" Freezer + 24" Fridge - Stainless Steel Integrated Columns

Model no:

RS1884FLJ1 / RS1884FLJK1 + RS2484SR1 / RS2484SRK1 shown.

(Various models available to swap units to opposite sides, hinge doors both left, both right or at the outsides as shown here).

(refer page 1 for imperial measurements)

IMPORTANT!

For ease of installation, ensure cavity has consistent dimensions top to bottom and left to right.

Clearance Dimensions	mm
Ⓐ Overall height of cavity	2134
Ⓑ Overall width of cavity	1067
Ⓒ Minimum depth of cavity*	635
Ⓓ Width of supply area behind freezer	457
Ⓔ Width of supply area behind fridge	610
Ⓕ Height of supply area	229
Ⓖ Height at sides of supply area	127
Ⓗ Width from side of supply area	13
Ⓘ Combined width in from side of supply areas	25
⓵ Depth of supply area	25
Minimum door cabinetry gap clearance	3


Optional Stainless Steel Panel Dimensions	mm
Ⓚ Height of door panel	2029
Ⓛ Width of freezer door panel	451
Ⓜ Width of fridge door panel	603
Ⓝ Depth of door panels	19
Ⓞ Height of toekick panel	100
Ⓟ Width of toekick panel	1063

* With cavity at minimum depth, electrical and water connections must be within the supply area shown if located behind the appliance, and must not protrude from the back wall. Connections may be located in an adjacent cabinet to either side of the fridge.

HANDLES: Handle Kits are sold separately. Shown with handle kit ADH3-RD84. Other style options available.

DATE: 10.10.2018

IMPORTANT NOTE: Throughout this guide, dimensions may vary by ±2mm (1/16"). Please read the installation manual for detailed information on installing the product. For full installation instructions & specifications visit fisherpaykel.com



ISO VIEW OF 1067mm CAVITY
(457mm + 610mm)