DLEX8900B / DLGX8901B

9.0 cu. ft. TurboSteam® Front Load Dryer

- 9.0 cu. ft. Mega Capacity
- TurboSteam® Technology
- SteamSanitary[™] and SteamFresh[™] Cycle
- Al Fabric Sensor / Smart Pairing $^{\text{\tiny M}}$
- 12 Cycles / 12 Options
- Sensor Dry System
- FlowSense™ Duct Clogging and Lint Filter Indicators
- NeveRust[™] Stainless Steel Drum
- LG ThinQ® Technology (Wi-Fi)










Drum Light Yes Control Lock Yes FlowSense™ Duct Clogging Indicator End of Cycle Signal Yes Remaining Time Display / Status Indicator(s) Reversible Door Yes Venting Option Electric: 4 Way Venting Gas: 3 Way Venting 3 Minute Installation Check Yes Leveling Legs 4 Adjustable Legs ADA Compliant No SMART FEATURES Wi-Fi Enabled Yes ThinQ® Technology Yes SmartDiagnosis™ Yes Remote Monitoring & Yes Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Glass / Chrome Door Cover Dark Blue Tinted Square Cover
Control Lock FlowSense™ Duct Clogging Indicator End of Cycle Signal Remaining Time Display / Status Indicator(s) Reversible Door Venting Option Electric: 4 Way Venting Gas: 3 Way Venting 3 Minute Installation Check Leveling Legs 4 Adjustable Legs ADA Compliant No SMART FEATURES Wi-Fi Enabled Yes ThinQ® Technology ThinQ Care SmartDiagnosis™ Yes Remote Monitoring & Yes Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Glass / Chrome
FlowSense™ Duct Clogging Indicator End of Cycle Signal Remaining Time Display / Status Indicator(s) Reversible Door Venting Option Electric: 4 Way Venting Gas: 3 Way Venting 3 Minute Installation Check Leveling Legs 4 Adjustable Legs ADA Compliant No SMART FEATURES Wi-Fi Enabled ThinQ® Technology ThinQ Care SmartDiagnosis™ Yes Remote Monitoring & Notifications MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Yes
Indicator End of Cycle Signal Remaining Time Display / Status Indicator(s) Reversible Door Yes Venting Option Electric: 4 Way Venting Gas: 3 Way Venting 3 Minute Installation Check Leveling Legs 4 Adjustable Legs ADA Compliant No SMART FEATURES Wi-Fi Enabled Yes ThinQ® Technology Yes SmartDiagnosis™ Yes Remote Monitoring & Yes Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Glass / Chrome
Remaining Time Display / Status Indicator(s) Reversible Door Venting Option Electric: 4 Way Venting Gas: 3 Way Venting 3 Minute Installation Check Leveling Legs ADA Compliant No SMART FEATURES Wi-Fi Enabled Yes ThinQ® Technology ThinQ Care SmartDiagnosis™ Yes Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Yes NeveRust™ Stainless Steel Glass / Chrome
Indicator(s) Reversible Door Venting Option Electric: 4 Way Venting Gas: 3 Way Venting 3 Minute Installation Check Yes Leveling Legs 4 Adjustable Legs ADA Compliant No SMART FEATURES Wi-Fi Enabled Yes ThinQ® Technology Yes ThinQ Care SmartDiagnosis™ Yes Remote Monitoring & Notifications MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Glass / Chrome
Venting Option Electric: 4 Way Venting Gas: 3 Way Venting 3 Minute Installation Check Yes Leveling Legs 4 Adjustable Legs ADA Compliant No SMART FEATURES Wi-Fi Enabled ThinQ® Technology Yes ThinQ Care SmartDiagnosis™ Yes Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Electric: 4 Way Venting Gas: 3 Way Venting Yes 4 Adjustable Legs 4 Adjustable Legs Yes Yes Yes ThinQ® Technology Yes Yes Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Glass / Chrome
Gas: 3 Way Venting 3 Minute Installation Check Yes Leveling Legs 4 Adjustable Legs ADA Compliant No SMART FEATURES Wi-Fi Enabled Yes ThinQ® Technology Yes ThinQ Care Yes SmartDiagnosis™ Yes Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Glass / Chrome
Leveling Legs 4 Adjustable Legs ADA Compliant No SMART FEATURES Wi-Fi Enabled Yes ThinQ® Technology Yes ThinQ Care Yes SmartDiagnosis™ Yes Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Glass / Chrome
ADA Compliant SMART FEATURES Wi-Fi Enabled ThinQ® Technology Yes ThinQ Care SmartDiagnosis™ Yes Remote Monitoring & Notifications MATERIALS AND FINISHES Drum Material Door / Rim No No No No No No No No No N
SMART FEATURES Wi-Fi Enabled ThinQ® Technology Yes ThinQ Care SmartDiagnosis™ Yes Remote Monitoring & Notifications MATERIALS AND FINISHES Drum Material Door / Rim Yes NeveRust™ Stainless Steel Glass / Chrome
Wi-Fi Enabled Yes ThinQ® Technology Yes ThinQ Care Yes SmartDiagnosis™ Yes Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material Door / Rim Yes NeveRust™ Stainless Steel Glass / Chrome
ThinQ® Technology Yes ThinQ Care Yes SmartDiagnosis™ Yes Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material Door / Rim Ves NeveRust™ Stainless Steel Glass / Chrome
ThinQ Care SmartDiagnosis™ Yes Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material Door / Rim Yes Yes Yes Yes Glass / Chrome
SmartDiagnosis™ Yes Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Glass / Chrome
Remote Monitoring & Yes Notifications MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Glass / Chrome
MATERIALS AND FINISHES Drum Material NeveRust™ Stainless Steel Door / Rim Glass / Chrome
Drum MaterialNeveRust™ Stainless SteelDoor / RimGlass / Chrome
Door / Rim Glass / Chrome
Door Cover Dark Plus Tinted Square Cover
Dark Dide Hillen Strate Cover
TECHNICAL SPECS
Electrical Requirements Electric: 240V, 30 Amps Gas: 120V, 15 Amps
Gas Dryer BTU Rating 20,000
Power Outlet Location Within 48" of Either Side
Plug Type Gas: 3-Prong (Cord Attached to Unit) Electric: 4-Wire (Cord Required)
ENERGY STAR® Certified Yes
Combined Energy Factor (CEF) Electric: 3.94 / Gas: 3.49

COLOR AVAILABILITY			
DLEX8900B (Electric) – Black Steel			
DLGX8901B (Gas) – Black Steel			
CAPACITY & MATCHING WASHER			
Capacity (cu. ft.)	9.0		
Matching Washer	WM8900HBA		
APPEARANCE	WWOSCOTIBA		
Electronic Controls with LED Display	Yes		
Touch Buttons	Yes		
Dial-A-Cycle [™]	Yes		
DRYER CYCLES			
Number of Cycles	12		
Sensor Dry Cycles	Normal, Perm Press, Towels, Delicates, Heavy Duty SteamFresh™, SteamSanitary™, Bedding, Small Load		
Manual Dry Cycles	Speed Dry, Air Dry, Downloaded		
DRYER OPTIONS			
Number of Options	12		
Options	TurboSteam®, Damp Dry Signal, More Time, Less Time, Wrinkle Care, Energy Saver, Control Lock, Reduce Static, Signal, Drum Light, Wi-Fi, Remote Start		
Temperature Settings	High, Medium High, Medium, Low, Ultra Low		
Drying Levels	Very Dry, More Dry, Normal Dry, Less Dry, Damp Dry		
Manual Dry Times	60 min., 50 min., 40 min., 30 min., 20 min., More Time / Less Time		
FABRIC CARE			
Steam Technology	TurboSteam®		
Sensor Dry	Yes		
Precise Temperature Control with Variable Heater	Yes		

OPTIONAL ACCESSORIES		
Pedestal	WDP5B	
Pedestal (W x H x D)	29" x 14 1/8" x 30 7/8"	
Stacking Kit	KSTK2	
Drying Rack	MGR62082001	
LP Conversion Kit	383EEL3002D	
Side Vent Kit	383EEL9001L	

DIMENSIONS		
Product (W x H x D)	29" x 40 3/4 " x 32 1/8 "	
Depth with Door Open	59"	
Cutout Dimensions (W x H x D)	31" x 41" x 37 ¹ / ₈ " (34 ¹ / ₈ " D for Side or Bottom Venting)	
Carton Dimensions (W x H x D)	31 1/2" x 45 1/8" x 33 7/8"	
Approx. Weight (Product / Carton)	Electric: 155 lbs. / 170.6 lbs. Gas: 161 lbs. / 171.5 lbs.	
LIMITED WARRANTY		
Parts and Labor	1 Year	
Dryer Drum	3 Years (Parts Only)	

DIMENSIONS / CLEARANCES



SPACING FOR RECESSED AREA OR CLOSET INSTALLATION


The following clearances are recommended for the appliance.


- · Additional clearances should be considered for ease of installation and servicing.
- Additional clearances should be considered on all sides of the dryer to reduce noise transfer.


CLOSET VENTILATION REQUIREMENTS

Closets with doors must have both an upper and lower vent to prevent heat and moisture buildup in the closet. One upper vent opening with a minimum opening of 48 sq. in. (310 cm2) must be installed no lower than 6 feet above the floor. One lower vent opening with a minimum opening of 24 sq. in. (155 cm2) must be installed no more than one foot above the floor. Install vent grilles in the door or cut down the door at the top and bottom to form openings. Louvered doors with equivalent ventilation openings are also acceptable.

- There should be at least a little space around the dryer (or any other appliance) to eliminate the transfer of vibration from one appliance to another. If there is enough vibration, it could cause appliances to make noise or come into contact, causing paint damage and further increasing noise.
- No other fuel-burning appliance can be installed in the same closet as a dryer.








DIMENSIONS / CLEARANCES


INSTALLATION SPACING FOR RECESSED AREA OR CLOSET, WITH STACKED WASHER AND DRYER



†Differs depending on the washer dimensions.

CLEARANCES WITH OPTIONAL PEDESTAL BASE

For cabinet installation with a door, minimum ventilation openings in the top of the cabinet are required.



VENTING THE DRYER

- If connecting to existing ductwork, make sure it is suitable and clean before installing the dryer.
- Venting must conform to local building codes.
- · Gas dryers MUST exhaust to the outdoors.
- Use only 4-inch (10.2 cm) rigid, semi-rigid or flexible metal ductwork inside the dryer cabinet and for venting outside.
- The exhaust duct must be 4 inches (10.2 cm) in diameter with no obstructions. The exhaust duct should be kept as short as possible. Make sure to clean any old ducts before installing your new dryer.
- Rigid, semi-rigid or flexible metal ducting is recommended for use between the dryer and the wall. All non-rigid metal transition duct must be UL-listed. Use of other materials for transition duct could affect drying time.
- Ductwork is not provided with the dryer. You should obtain the necessary ductwork locally.
 - The vent hood should have hinged dampers to prevent backdraft when the dryer is not in use.
- The total length of flexible metal duct must not exceed 8 ft. (2.4 m).

NOTE

Deduct 6 ft. (1.8 m) for each additional elbow. Do not use more than four 90° elbows.

DUCTWORK

Wall Cap Type	Number of 90° Elbows	Maximum length of 4-inch diameter rigid metal duct
Recommended (102 mm) (102 mm)	0	65 ft. (19.8 m)
	1	55 ft. (16.8 m)
	2	47 ft. (14.3 m)
	3	36 ft. (11.0 m)
	4	28 ft. (8.5 m)
Use only for short run installations 2 1/2" (635 mm)	0	55 ft. (16.8 m)
	1	47 ft. (14.3 m)
	2	41 ft. (12.5 m)
	3	30 ft. (9.1 m)
	4	22 ft. (6.7 m)

ROUTING AND CONNECTING DUCTWORK

NOTE:

Follow the guidelines below to maximize drying performance and reduce lint buildup and condensation in the ductwork. Ductwork and fittings are NOT included and must be purchased separately.

- Use 4-inch (10.2 cm) diameter rigid, semi-rigid or flexible metal ductwork.
- The exhaust duct run should be as short as possible.
- Use as few elbow joints as possible.
- The male end of each section of exhaust duct must point away from the dryer.
- Use duct tape on all duct joints.
- Insulate ductwork that runs through unheated areas in order to reduce condensation and lint buildup on duct surfaces.
- Incorrect or inadequate exhaust systems are not covered by the dryer warranty. Dryer failures or service required because of such exhaust systems will not be covered by the dryer warranty.

CONNECTING GAS DRYERS


Gas Supply Requirements

- As shipped from the factory, this dryer is configured for use with natural gas (NG). It can be converted for use with propane (LP) gas. Gas pressure must not exceed 8-inch (20.4 cm) water column for NG, or 13-inch (33.1 cm) water column for LP.
- A qualified service or gas company technician must connect the dryer to the gas service.

Electrical Requirements for Gas Models Only

- This dryer must be plugged into a 120-VAC, 60-Hz. grounded outlet protected by a 15-ampere fuse or circuit breaker.
- This dryer is equipped with a three-prong grounding plug for protection against shock hazard and should be plugged directly into a properly grounded three-prong receptacle. Do not cut or remove the grounding prong from this plug.

ELECTRIC & GAS CONNECTION LOCATIONS



CONNECTING ELECTRIC DRYERS

Electrical Requirements for Electric Models Only

- This dryer must be connected to a grounded metal, permanent wiring system, or an equipment-grounding conductor must be run with the circuit conductors and connected to the equipment-grounding terminal or lead on the dryer.
- The dryer has its own terminal block that must be connected to a separate 240 VAC, 60-Hertz, single-phase circuit, fused at 30 amperes (the circuit must be fused on both sides of the line). ELECTRICAL SERVICE FOR THE APPLIANCE SHOULD BE OF THE MAXIMUM RATE VOLTAGE LISTED ON THE NAMEPLATE. DO NOT CONNECT THE APPLIANCE TO 110-, 115-, OR 120-VOLT CIRCUIT.
- If the branch circuit to dryer is 15 ft. (4.5 m) or less in length, use UL (Underwriters Laboratories) listed No.-10 AWG wire (copper wire only), or as required by local codes. If over 15 ft. (4.5 m), use UL-listed No.-8 AWG wire (copper wire only), or as required by local codes. Allow sufficient slack in wiring so the dryer can be moved from its normal location when necessary.
- The power cord (pigtail) connection between the wall receptacle and the dryer terminal block IS NOT supplied with the dryer. Type of pigtail and gauge of wire must conform to local codes.



FOUR-WIRE POWER CORD

- A 4-wire connection is required for all mobile and manufactured home installations, as well as all new construction after January 1, 1996.
- · A UL-listed strain relief is required.
- Use a 30-amp, 240-volt, 4-wire, UL-listed power cord with #10 AWG-minimum copper conductor and closed loop or forked terminals with upturned ends.



FOUR-WIRE DIRECT WIRE

the dryer.

- A 4-wire connection is required for all mobile and manufactured home installations, as well as all new construction after January 1, 1996.
- · A UL-listed strain relief is required.
- Use UL-listed 4-wire #10 AWG minimum copper conductor cable. Allow at least 5 ft. (1.5 m) of wire to allow for removal and reinstallation of

