## DLEX5500\_ / DLGX5501\_

### 7.4 cu. ft. TurboSteam® Front Load Dryer

- 7.4 cu. ft. Ultra Large Capacity
- Digital Dial Control with LCD Display & Touch Buttons
- TurboSteam® Technology
- Al Fabric Sensor/ Smart Pairing™
- SteamSanitary<sup>™</sup> and SteamFresh<sup>™</sup> Cycle
- 23 Cycles / 11 Options
- Sensor Dry System

Manual Dry Times

- FlowSense<sup>™</sup> Duct Clogging Indicator
- NeveRust<sup>™</sup> Stainless Steel Drum
- LG ThinQ® Technology (Wi-Fi)









COLOR AVAILABILITY				
COLOR AVAILABILITY		FABRIC CARE	TurboSteam®	
DLEX5500V (Electric) – Graphite Steel		Steam Technology		
DLGX5501V (Gas) – Graphite Steel		Al Sensor Dry™	Yes	
DLEX5500W (Electric) – White		Sensor Dry Precise Temperature Control	Yes Yes	
		with Variable Heater	165	
DLGX5501W (Gas) – White		CONVENIENCE		
CAPACITY & MATCHING WA	ASHER	Drum Light (Door Open)	Yes	
Capacity (cu. ft.)	7.4	Control Lock	Yes	
Matching Washer  APPEARANCE	WM5500HWA, WM5500HVA	FlowSense <sup>™</sup> Duct Clogging Indicator	Yes	
Electronic Controls with LCD	Yes	End of Cycle Signal	Yes	
Display Touch Buttons	Yes	Remaining Time Display / Status Indicator(s)	Yes	
Dial-A-Cycle™	Yes	Reversible Door	Yes	
DRYER CYCLES Number of Cycles	23	Venting Option	Electric: 4 Way Venting Gas: 3 Way Venting	
Sensor Dry Cycles	Normal, AI Dry, Bedding, Delicates, Towels, Quick Dry, Timed Dry, Power Dry, Perm. Press, SteamFresh™, Heavy Duty, Air Dry, Steam Sanitary™, Super Dry, Active Wear, Jeans, Blanket Refresh, Low Temp Dry, Overnight Dry, Easy Ironing, Small Load, Large Load Dry, X Large Load Dry	3 Minute Installation Check	Yes	
, ,		Leveling Legs	4 Adjustable Legs	
		ADA Compliant	No	
		SMART FEATURES		
		Wi-Fi Enabled	Yes	
		ThinQ® Technology	Yes	
		ThinQ Care	Yes	
		Voice Control	Google Assistant, Amazon Alex	
DRYER OPTIONS		SmartDiagnosis <sup>™</sup>	Yes	
Number of Options	11	Remote Start (On / Off)	Yes	
Options	Cycle Optimization, Damp Dry Signal, Wrinkle Care, Control Lock, Wi-Fi, Energy Saver, TurboSteam®, Reduce Static, Remote Start, Drum Light, Signal, Cycle Edit List	Remote Monitoring & Notifications	Yes	
		MATERIALS AND FINISHES		
		Drum Material	NeveRust™ Stainless Steel	
		Cabinet	Painted Steel	
Temperature Settings	High, Med. High, Medium, Low,	Door / Rim	Glass / Chrome	
Drying Levels	Ultra Low  Very Dry, More Dry, Normal Dry,	Door Cover	Tempered Glass Door	
	Less Dry, Damp Dry			

10 min ~ 100 min (Every 10 min)

TECHNICAL SPECS		
Electrical Requirements	Elec: 120/240V, 60Hz, 26A Gas: 120V, 60Hz, 11.5A	
Gas Dryer BTU Rating	20,000	
Power Outlet Location	Within 24" of Either Side	
Plug Type	Gas: 3-Prong (Cord Attached to Unit) Electric: 4-Wire (Cord Required)	
ENERGY STAR® Certified	Yes	
Combined Energy Factor (CEF)	Electric: 3.94 Gas: 3.49	


		ACCE	ccn	D
INCLU	JUEU	ACCE	<u> </u>	MI-E


Y Connector


OPTIONAL ACCESSORIES	
Pedestal	WDP6W, WDP6V
Pedestal (W x H x D)	27" x 13 5/8" x 28" (43 7/8" D with Door Open)
ADA-Compliant Pedestal Riser	WDPS2W (White)
ADA-Compliant Pedestal Riser (W x H x D)	27" x 5 1/8" x 27 1/2"

Stacking Kit	KSTK4	
Drying Rack	3750EL1001A	
LP Conversion Kit	383EEL3002D	
Side Vent Kit	3911EZ9131X (Interchangeable with 383EEL9001B)	
DIMENSIONS		
Product (W x H x D)	27" x 39" x 29 <b>3</b> / <b>4</b> "	
Depth with Door Open	51 <b>3</b> /8"	
Cutout Dimensions (W x H x D)	29" x 39 1/4" x 35" (32" D for Side or Bottom Venting)	
Carton Dimensions (W x H x D)	28 <b>7</b> / <sub>8</sub> " x 43 <b>1</b> / <sub>8</sub> " x 31 <b>3</b> / <sub>8</sub> "	
Approx. Weight (Product / Carton)	Electric: 124.3 lbs. / 136.5 lbs. Gas: 136.0 lbs. / 146.6 lbs.	
LIMITED WARRANTY		
Parts and Labor	1 Year	
Dryer Drum	3 Years (Parts Only)	

#### **DIMENSIONS / CLEARANCES**







- \* Required spacing
- \*\* For side or bottom venting, 2-inch (51 mm) of spacing is allowed.


#### SPACING FOR RECESSED AREA OR CLOSET INSTALLATION

The following clearances are recommended for this dryer. This dryer has been tested for clearances of 1 inch (2.5 cm) on the sides and rear. Recommended clearances should be considered for the following reasons:

- Additional clearances should be considered for ease of installation and servicing.
- Additional clearances should be considered on all sides of the dryer to reduce noise transfer. For closet installation, with a door, minimum ventilation openings in the top and bottom of the door are required. Louvered doors with equivalent ventilation openings are acceptable.


#### **Closet Ventilation Requirements**

Closets with doors must have both an upper and lower vent to prevent heat and moisture buildup in the closet. One upper vent opening with a minimum opening of 48 sq. in. (310 cm²) must be installed no lower than 6 feet above the floor. One lower vent opening with a minimum opening of 24 sq. in. (155 cm²) must be installed no more than one foot above the floor. Install vent grills in the door or cut down the door at the top and bottom to form openings. Louvered doors with equivalent ventilation openings are also acceptable.



#### **DIMENSIONS / CLEARANCES**


#### INSTALLATION SPACING FOR RECESSED AREA OR CLOSET, WITH STACKED WASHER AND DRYER



- \* Required spacing
- \*\* For side or bottom venting, 2-inch (51 mm) of spacing is allowed.
- † Differs depending on the washer dimensions.

#### INSTALLATION SPACING FOR CABINET

For cabinet installation with a door, minimum ventilation openings in the top of the cabinet are required.



#### **VENTING THE DRYER**

- If connecting to existing ductwork, make sure it is suitable and clean before installing the dryer.
- Venting must conform to local building codes.
- Gas dryers MUST exhaust to the outdoors.
- Use only 4-inch (10.2 cm) rigid, semi-rigid or flexible metal ductwork inside the dryer cabinet and for venting outside.
- The exhaust duct must be 4 inches (10.2 cm) in diameter with no obstructions. The exhaust duct should be kept as short as possible. Make sure to clean any old ducts before installing your new dryer.
- Rigid, semi-rigid or flexible metal ducting is recommended for use between the dryer and the wall. All non-rigid metal transition duct must be UL-listed. Use of other materials for transition duct could affect drying time.
- Ductwork is not provided with the dryer. You should obtain the necessary ductwork locally.
- The vent hood should have hinged dampers to prevent backdraft when the dryer is not in use.
- The total length of flexible metal duct must not exceed 8 ft. (2.4 m).

#### NOTE

Deduct 6 ft. (1.8 m) for each additional elbow. Do not use more than four 90° elbows.

#### **DUCTWORK**

Wall Cap Type	Number of 90° Elbows	Maximum length of 4-inch diameter rigid metal duct
Recommended  (102 mm)	0	65 ft. (19.8 m)
	1	55 ft. (16.8 m)
	2	47 ft. (14.3 m)
	3	36 ft. (11.0 m)
	4	28 ft. (8.5 m)
Use only for short run installations  2 1/2" (635 mm)	0	55 ft. (16.8 m)
	1	47 ft. (14.3 m)
	2	41 ft. (12.5 m)
	3	30 ft. (9.1 m)
	4	22 ft. (6.7 m)

#### ROUTING AND CONNECTING DUCTWORK

#### NOTE:


Follow the guidelines below to maximize drying performance and reduce lint buildup and condensation in the ductwork. Ductwork and fittings are NOT included and must be purchased separately.

- Use 4-inch (10.2 cm) diameter rigid, semi-rigid or flexible metal ductwork.
- The exhaust duct run should be as short as possible.
- Use as few elbow joints as possible.
- The male end of each section of exhaust duct must point away from the dryer.
- Use duct tape on all duct joints.
- Insulate ductwork that runs through unheated areas in order to reduce condensation and lint buildup on duct surfaces.
- Incorrect or inadequate exhaust systems are not covered by the dryer warranty. Dryer failures or service required because of such exhaust systems will not be covered by the dryer warranty.

# CORRECT VENTING

#### CONNECTING THE WATER INLET HOSE (STEAM DRYERS ONLY)

The dryer must be connected to the cold water tap using the new water supply hose. Do not reuse old hoses.



#### CONNECTING GAS DRYERS


#### Gas Supply Requirements

- As shipped from the factory, this dryer is configured for use with natural gas (NG). It can be converted for use with propane (LP) gas. Gas pressure must not exceed 8-inch (20.4 cm) water column for NG, or 13-inch (33.1 cm) water column for LP.
- A qualified service or gas company technician must connect the dryer to the gas service.

#### **Electrical Requirements for Gas Models Only**

- This dryer must be plugged into a 120-VAC, 60-Hz. grounded outlet protected by a 15-ampere fuse or circuit breaker.
- This dryer is equipped with a three-prong grounding plug for protection against shock hazard and should be plugged directly into a properly grounded three-prong receptacle. Do not cut or remove the grounding prong from this plug.

#### **ELECTRIC & GAS CONNECTION LOCATIONS**



#### CONNECTING ELECTRIC DRYERS

#### **Electrical Requirements for Electric Models Only**

- This dryer must be connected to a grounded metal, permanent wiring system, or an equipment-grounding conductor must be run with the circuit conductors and connected to the equipment-grounding terminal or lead on the dryer.
- The dryer has its own terminal block that must be connected to a separate 240 VAC, 60-Hertz, single-phase circuit, fused at 30 amperes (the circuit must be fused on both sides of the line). ELECTRICAL VOLTAGE LISTED ON THE NAMEPLATE. DO NOT CONNECT THE DRYER TO 110-, 115-, OR 120-VOLT CIRCUIT.
- If the branch circuit to dryer is 15 ft. (4.5 m) or less in length, use UL (Underwriters Laboratories) listed No.-10 AWG wire (copper wire only), or as required by local codes. If over 15 ft. (4.5 m), use UL-listed No.-8 AWG wire (copper wire only), or as required by local codes. Allow sufficient slack in wiring so the dryer can be moved from its normal location when necessary.
- The power cord (pigtail) connection between the wall receptacle and the dryer terminal block IS NOT supplied with the dryer. Type of pigtail and gauge of wire must conform to local codes



#### **FOUR-WIRE POWER CORD**

- A 4-wire connection is required for all mobile and manufactured home installations, as well as all new construction after January 1, 1996.
- · A UL-listed strain relief is required.
- Use a 30-amp, 240-volt, 4-wire, UL-listed power cord with #10 AWG-minimum copper conductor and closed loop or forked terminals with upturned ends.



#### FOUR-WIRE DIRECT WIRE

- A 4-wire connection is required for all mobile and manufactured home installations, as well as all new construction after January 1, 1996.
- A UL-listed strain relief is required.
- Use UL-listed 4-wire #10 AWG minimum copper conductor cable. Allow at least 5 ft. (1.5 m) of wire to allow for removal and reinstallation of the dryer.

